


WiFi6E Flexible and PCB Antennas

WiFi6E Flexible and PCB Antennas, with upgraded triple-band antenna support, are designed for quick and easy integration into wireless devices at minimal implementation cost and enable high-performance RF transmission for demanding Wi-Fi applications.

FEATURES AND ADVANTAGES



MARKETS AND APPLICATIONS

Consumer

Connected Home Smart Home

Automotive

Connected Vehicle
Comfort and Infotainment

Industrial

Smart Cities





Connected Home

Smart Cities



WiFi6E Flexible and PCB Antennas >


FEATURES AND ADVANTAGES


Topside of the poly-flexible antenna

Makes for easy peel-and-stick mounting anywhere within the device chassis

Rigid PCB antenna with two holes on both sides for screw-nut mounting

Offers more robust securing of antenna to device chassis in rugged applications







WiFi6E Flexible and PCB Antennas >

SPECIFICATIONS

REFERENCE INFORMATION

Reference Information
Packaging: PET Film
Mates with: Surface-mount, I
-PEX MHF series receptacle
Designed In: Millimeters

RoHS: Yes Halogen Free: Yes Glow Wire Capable: No

ELECTRICAL

RF Power (Watt): 2 Return Loss: < -10 dB

Refer to Product Specifications (212330) Average Total Radiation Efficiency (%): Refer to Product Specifications

Peak Gain (dBi):Refer to Product Specifications

Input Impedance (ohms): 50

MECHANICAL

Refer to Product Specifications

PHYSICAL

Material: Flexi (146153, 204281, 208482, 206994, 212330, 219611); PCB (146187)

Plating:

Refer to Sales Drawings

Operating Temperature: -30 to +85°C -40 to +85°C (208482, 212330)

ORDERING INFORMATION

Series No.	Substrate	Cable Feed	Dimensions (mm)	Cable Lengths (mm)
206994	Flexi material	Side	15.00 by 6.00	100.00
208482	Flexi material	Center	55.20 by 19.20 by 0.16	100.00, 150.00, 200.00
204281	Flexi material	Side	35.00 by 11.00 by 0.10	50.00
				100.00
				150.00
				200.00
				250.00
				300.00
<u>146153</u>	Flexi material	Center	34.90 by 9.00 by 0.10	50.00
				100.00
				150.00
				200.00
				250.00
				300.00
<u>146187</u>	PCB (FR4)	Center	40.95 by 9.00 by 0.70	50.00
				100.00
				150.00
				200.00
				250.00
				300.00
<u>212330</u>	Flexi material	Center	70.00 by 20.00	100.00, 150.00, 200.00
<u>219611</u>	Flexi material	Center	35.00 by 15.00 by 0.10	50.00, 100.00, 150.00, 200.00, 250.00, 300.00

www.molex.com/link/antenna_iot.html