

Woodhead Enabling Switch with Quick Connector

molex

The Woodhead Enabling Switch with Quick Connector was designed for demanding conditions where reliable on/off actuation is essential, providing a flexible means to control equipment during production, material handling, changeovers, setup, inspection, cleaning and troubleshooting

Features and Advantages

Handheld and safe for use
Eliminates the need for tools.
Decreases risk of injury

Ergonomic mold design
Offers easy implementation.
Decreases labor time

cULus approved
Ensures performance expectations. Meets standards for electrical safety

Made with Advanced Vulcanized Silicone Rubber; dust, oil and water resistant. Also available in Nitrile/PVC
Withstands impact, heat, harsh weather conditions and chemicals. Tolerates harsh industrial environments

Mini-Change Connector (7/8")
Delivers optimum conductivity. Environmental rating NEMA 3R, wet location

Tested for durability and is maintenance free
Provides long life cycle.
Delivers applied cost savings by eliminating the need for replacement parts



Applications

Industrial

- Assembly lines
- Material handling
- Maintenance
- Production
- Automotive assembly lines



Material Handling



Production Lines

Woodhead Enabling Switch with Quick Connector



Specifications

ELECTRICAL

Current and Voltage (max.):
10A, 125/250V AC, 1/2 hp

PHYSICAL

Weight: 0.25 lb.
Dimensions:
Length — 4.34"
Diameter — 1.25"
Connector: Mini-Change Connector 7/8"

ENVIRONMENTAL RATING

NEMA 3R, Wet Location

AGENCY APPROVALS

cULus

Ordering Information

ENABLING SWITCH

Part No.	Woodhead No.	No. of Pins	Throw	Pole Position	Body
130023-0001	55501	2	Single	Normally Open	Nitrile/PVC
130023-0002	55502	2	Single	Normally Closed	Nitrile/PVC
130023-0003	55503	3	Double	Normally Open/Normally Closed	Nitrile/PVC
130023-0004	55504	3	Single	Normally Open	Nitrile/PVC
130126-0364	55501S	2	Single	Normally Open	Silicone
130126-0365	55502S	2	Single	Normally Closed	Silicone
130126-0366	55503S	3	Double	Normally Open/Normally Closed	Silicone
130126-0367	55504S	3	Single	Normally Open	Silicone

ENABLING SWITCH ACCESSORIES

Part No.	Woodhead No.	No. of Pins	Description	Cord/Wire Length (feet)
130006-0091	102000A01F060	2	Single-Ended Cord Set	6
130006-0096	102000A01F120	2	Single-Ended Cord Set	12
130006-0102	102000A01F200	2	Single-Ended Cord Set	20
130010-0147	112020A01F060	2	Double-Ended Cord Set	6
130010-0152	112020A01F120	2	Double-Ended Cord Set	12
130010-0159	112020A01F200	2	Double-Ended Cord Set	20
130006-0221	103000A01F060	3	Single-Ended Cord Set	6
130006-0232	103000A01F120	3	Single-Ended Cord Set	12
130006-0241	103000A01F200	3	Single-Ended Cord Set	20
130010-0221	113020A01F060	3	Double-Ended Cord Set	6
130010-0228	113020A01F120	3	Double-Ended Cord Set	12
130010-0238	113020A01F200	3	Double-Ended Cord Set	20
130013-0060	1R2004A20A120	2	Panel Mount Female	1
130013-0135	1R3004A20A120	3	Panel Mount Female	1

www.molex.com/link/pushbuttonpendant.html

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.