

## SCORING GUIDE FOR SUPPLIER PERFORMANCE SCORECARD

Metric	Metric Weight	KPI Weight	KPI	1: Unacceptable	2	3: Meets Standard	4	5: Best in Class
Quality	65%	40%	<b>QN Rate and Severity</b>	L4 QN or more than 12 QNs (L1 or L2 or L3)	4 -12 QNs ( L1 or L2 or L3)	2-3 QNs ( L1 or L2 or L3)	1 QN (L1 or L2 or L3)	0 QN
		40%	<b>PPM - MG101</b>	>20,000	7001 - 20,000	2001 - 7000	51 - 2000	0 - 50
			<b>PPM - MG102</b>	>12,000	7001 - 12,000	2001 - 7000	101-2000	0 - 100
			<b>PPM - MG103</b>	>2501	1501 - 2500	501 - 1500	21 - 500	0 - 20
			<b>PPM - MG201</b>	>300,000	40,001 - 300,000	2001 - 40,000	51 - 2000	0 -50
			<b>PPM - MG202</b>	>300,000	100,001 - 300,000	10,001 - 100,000	101 - 10,000	0 - 100
			<b>PPM - MG203</b>	>100,000	20,001 - 100,000	4001 - 20,000	101-4000	0 - 100
			<b>PPM - MG204</b>	>80,000	20,001 - 80,000	5001 - 20,000	101 - 5000	0 - 100
			<b>PPM - MG206</b>	>100,000	30,001 - 100,000	3001 - 30,000	101 - 3000	0 - 100
			<b>PPM - MG207</b>	>100,000	10,001 - 100,000	2001 - 10,000	101 - 2000	0 - 100
			<b>PPM - MG208</b>	>15,000	8001 - 15,000	1001 - 8000	31 -1000	0 - 30
			<b>PPM - MG209</b>	>200,000	50,001 - 200,000	10,001 - 50,000	101-10,000	0 - 100
		<b>PPM - MG301</b>	>100,000	10,001 - 100,000	2001 - 10,000	101 - 2000	0 - 100	
	20%	<b>8D On-Time Completion</b>	Less than 50% on time	74% - 50% on time	84% - 75% on time	99% - 85% on time	100% 8D completed on time	
Assurance of Supply (Delivery)	35%	50%	<b>% on time to Molex Request Date (MRD)</b>	25% and below	50%-26% on time	70% - 51% on time	85% - 71% on time	More than 85% on time
		50%	<b>% on time to Supplier Promise Date (VPD)</b>	60% and below	70%-61% on time	80% - 71% on time	90% - 81% on time	More than 90% on time
<b>Total</b>	100%							